



NOTES:

1. MAX. MTG. TORQUE = 3lb-in.
2. HARDWARE IS INCLUDED.



LEAD FINISH:	SILVER
BUSHING FINISH:	SILVER
CAPACITANCE	1000pF +100/-0%
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C -- VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
100	N/A
500	N/A
1 GHz	N/A
10 GHz	N/A

SCHEMATIC




MARKING:

PART: S 102P

BAG:
SCI 779 001 102P
DATE CODE
QTY/BAG (200 MAX.)

02	01	00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED
CN. 213380	CN. 209912	CN. 185028	CHANGE NOTICE	Fractions ± 1/64
				Dec. .xx±
				Dec. .xxx±.005
				Angles ±0° 30'
				CODE IDENT. NO. DLSP2



ERIE, FAIRVIEW
PENNSYLVANIA

Dwn. KAUFFMAN
Date 11/26/02
Engr. Joe V.
Scale NONE

Description FEED THRU
RESIN SEAL FILTER
54779001X5U102P