


 **PRODUCT CATALOG**
[English](#) [日本語](#)

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Help/Glossary](#)

Circuit Protection Devices

↳ PolySwitch Resettable Devices

Raychem RXE135

[Active](#)
**Directive 2000/53/EC
Compliant**
[ELV Compliant](#)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info	Pricing Product Availability	

Searchable Features:	
Brand:	Raychem
Family Name:	RXE
Form Factor:	Radial Leaded
IH [Room Temperature] (Amps.):	1.350
IT [Room Temperature] (Amps.):	2.70
Operating Voltage, Max.:	72.0 V
Interrupt Current, Max. (Amps.):	40
Time To Trip (Amps.):	6.75
Time To Trip (Seconds):	9.60
Resistance [@ room temp] (Ω):	0.1550
Rmin (Ω):	0.1200
Rmax (Ω):	0.19000
R1 Max [Post Trip] (Ω):	0.3000
Available Binned:	No

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)