





UNIT:mm



CONN OUTER MOLD: WM-020

P1




CONN OUTER MOLD: WM-020

P2

PIN ASSIGNMENT			
P1	RED	P2	
1	WHITE	1	
2	SPIRAL	2	
3		3	

Electronic Test:
1.100% Test,(Open,Short,Miss Wire)
2.Contact Resistance:2 ohm max.
3.Insulation Resistance:1M ohm min.
4.Hi-Pot:100V DC/10ms



1PCS/PE BAG

⑦	TIE	1	BLACK L=80mm
⑥	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*L15mm.
⑤	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
④	PE BAG	1	CLEAR SIZE:100*200*0.05mm PRINT BLACK"MADE IN CHINA".
③	OUT JACKET	5.5g	OUTER MODEL PVC 45P COLOR BLACK
②	CONN	2	3.5ST MALE Tray6.0mm L=30mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
①	CABLE	1	NOUL 28AWG(7/0.12 TC)*2C(RED,WHITE)+S(43/0.12 TC) JACKET BLACK OD:3.0MM L=2020±20mm.
NO.	NAME	Q'TY	SPECIFICATION

Cnc Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	770-10040-00200
DECIDE BY		DATE	2012-02-15
VERSIONS/EDITEDN	A/0	PROJECTION	