


## T-1 3/4 Midget Flange Base



| Part Number | Design Voltage | Amps | MSCP  | Life Hours | Filament Type |
|-------------|----------------|------|-------|------------|---------------|
| CM331       | 1.35           | .060 | .010  | 500        | C-6           |
| CM268       | 2.50           | .350 | .200  | 10,000     | C-2R          |
| CM343       | 2.50           | .400 | .550  | 30         | C-2R          |
| CM368       | 2.50           | .200 | .220  | 500        | C-2R          |
| CM338       | 2.70           | .060 | .040  | 6,000      | C-2R          |
| CM375       | 3.00           | .015 | .004  | 10,000     | C-6           |
| CM8848      | 3.00           | .350 | .300  | 10,000     | C-2R          |
| CM7331      | 4.50           | .120 | .050  | 25,000     | C-2R          |
| CM3150      | 5.00           | .060 | .150  | 5,000      | C-2R          |
| CM7332      | 5.00           | .060 | .030  | 60,000     | C-2R          |
| CM7333      | 5.00           | .060 | .050  | 25,000     | C-2R          |
| CM7334      | 5.00           | .190 | .450  | 1,000      | C-2R          |
| CM7335      | 5.00           | .115 | .150  | 40,000     | C-2R          |
| CM328       | 6.00           | .200 | .600* | 1,000      | C-2R          |
| CM345       | 6.00           | .040 | .030  | 10,000     | C-2V          |
| CM7336      | 6.00           | .200 | .100  | 50,000     | C-2F          |
| CM349       | 6.30           | .200 | .550  | 5,000      | C-2R          |
| CM350       | 6.30           | .150 | .450  | 3,000      | C-2R          |
| CM377       | 6.30           | .075 | .230  | 1,000      | C-2R          |
| CM380       | 6.30           | .040 | .020  | 20,000     | C-2V          |
| CM381       | 6.30           | .200 | .400  | 20,000     | C-2F          |
| CM344       | 10.0           | .014 | .002  | 50,000     | C-2F          |
| CM367       | 10.0           | .040 | .080  | 5,000      | C-2F          |
| CM7338      | 11.0           | .022 | .030  | 10,000     | C-2F          |
| CM394       | 12.0           | .040 | .120  | 10,000     | C-2F          |
| CM330       | 14.0           | .080 | .500  | 1,500      | C-2F          |
| CM382       | 14.0           | .080 | .300  | 15,000     | C-2F          |
| CM8918      | 14.0           | .100 | .500  | 10,000     | C-2F          |
| CM370       | 18.0           | .040 | .150  | 10,000     | C-2F          |
| CM459       | 22.0           | .040 | .300  | 2,000      | C-2F          |
| CM8176      | 24.0           | .050 | .500  | 1,000      | C-2F          |
| CM327       | 28.0           | .040 | .340  | 4,000      | C-2F          |
| CM376       | 28.0           | .060 | .340  | 25,000     | C-2F          |
| CM385       | 28.0           | .040 | .150  | 10,000     | C-2F          |
| CM387       | 28.0           | .040 | .300  | 7,000      | C-2F          |
| CM6034      | 28.0           | .024 | .150  | 4,000      | CC-2F         |
| CM7341      | 28.0           | .065 | .650  | 5,000      | C-2F          |
| CM269       | 32.0           | .040 | .300  | 4,000      | C-2F          |
| CM6848      | 48.0           | .025 | .200  | 5,000      | CC-2F         |

\* Lamp MSCP is .340 @ 5.0V