



*Quality Products. Service Excellence.*

## 20° Rack Consoles 1564 Series

Load rated to 600 lbs (272 kg)

**Note:** This product line has been discontinued as a stocked series. Information is for reference only. For alternative solution assistance, please **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



Available by special order.

### Features


- Constructed in 14-gauge steel (frame) and 14-gauge steel (rails).
- Choice of two depths, 24.5", and 31.5" usable depth.
- 20° Sloped panel height of 17.5" (10 U).
- Front panel height of 26.25" (15U).
- Finished in textured RAL9005 black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- 600 lbs (272 kg) **static load rating**.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.


### Unit is Shipped Complete with

- Two (2) pairs of EIA-compliant pre-installed upper and lower round hole-punched **combination rails**.
  - Starter pack of **1421N25** clip nuts
- One (1) Set of four (4) leveling feet

### Accessories

- Rack Shelves
- Rack Panels
- Equipment Cooling
- Rack Mount Desk
- We Manufacture PDUs and Outlet Strips
- Cable Managers
- Hardware for Rack Mounting Solutions





1564 Frame and Side Panels

| Part No.  | Overall Dimensions |           |           | Mounting  |       |       | Mounting Dimentions      |                        |                        |                       |
|-----------|--------------------|-----------|-----------|-----------|-------|-------|--------------------------|------------------------|------------------------|-----------------------|
|           | Height             | Width (A) | Depth (B) | Width (C) | E     | F     | Top (D) Fixed Rack Units | Upper Front Rack Units | Lower Front Rack Units | Rear Fixed Rack Units |
| 1564A2BK1 | 49.89              | 22.56     | 24.50     | 19.06     | 17.50 | 21.31 | 8U                       | 10U                    | 15U                    | 24U                   |
| 1564B2BK1 | 49.89              | 22.56     | 31.50     | 19.06     | 24.50 | 19.56 | 12U                      | 10U                    | 15U                    | 24U                   |

Side Panels Sold in Pairs

1564 Doors

| Door Type | Part No.     | Part No.     |
|-----------|--------------|--------------|
|           | Front Door   | Rear Door    |
| Solid     | RSDF19026BK1 | RSDF19042BK1 |
| Louvered  | RSDL19026BK1 | RSDL19042BK1 |

Doors are constructed of 18 gauge steel and feature lockable latch.

1564 Top Panels

| For Use    | Rack  | Part No.     | Part No.             | Part No.           | Part No.                |
|------------|-------|--------------|----------------------|--------------------|-------------------------|
| With Frame | Units | Solid Panel  | Vented Steel Panel   | Raised Solid Panel | Solid Side Panel (Pair) |
| 1564A2BK1  | 8U    | PBPS19014BK2 | Qty 2 x PPFS19007BK2 | PBRS19014BK2       | 1564APBK1               |
| 1564B2BK1  | 12U   | PBPS19021BK2 | Qty 2 x PPFS19010BK2 | PBRS19021BK2       | 1564BPBK1               |

1564 Rack Rails

| Part No.     | Mounting Dimensions |        |
|--------------|---------------------|--------|
|              | Rack Units          | Height |
| RSRC00017BK3 | 10U                 | 17.00  |
| RSRC00026BK3 | 15U                 | 26.00  |

Data subject to change without notice

