



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		N1	REVISED PER ECO-11-005030	11MAR11	RK	HMR



1. ACCEPTS COAX CABLE WITH .095-.110 O.D. JACKETS AND .055-.065 DIELECTRIC O.D.
EXAMPLE: RG-174 AND RG-316

2. TIN PLATE PER ASTM-B-545.

3. INSTRUCTION SHEET NO.: 408-2472-2.


4. ON STRIP

5. ON STRIP, LEGS MUST BE BENT MANUALLY AFTER CRIMPING.


6. LOOSE PIECE PARTS WITH PREFORMED LEGS.

7. BRASS PER ASTM-B-36.


8. TIN-LEAD PLATE PER ASTM-B-545.




VIEW C




VIEW D




SECTION A-A



SECTION B-B




PCB LAYOUT



AS APPLIED BY APPLICATOR

VIEW E



AS APPLIED BY APPLICATOR

VIEW F

2	D	6	9-226176-2
2	C&F	5	9-226176-1
2	C&E	4	9-226176-0
8	D	6	226176-4
8	C&F	5	226176-3
8	C&E	4	226176-2
FINISH	VIEW	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. OBRINE 30JUN99	 TE Connectivity				
		CHK M. OBRINE 30JUN99					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. CABRILLO 30JUN99	NAME BRAID-PIC P.C. BOARD GROUND TERMINAL SINGLE CRIMP-SINGLE CONTACT			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -		PRODUCT SPEC —				
			APPLICATION SPEC —				
	MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO
SEE NOTE 7		SEE TABLE	.007 OZ	A2	00779	C-226176	—
CUSTOMER DRAWING				SCALE		SHEET	REV
				6:1		1 OF 1	N1