


TW-20-07-T-D-550-SM

TW-10-04-L-D-300-SM

TW SERIES

SMT BOARD STACKERS

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	SM	OTHER OPTIONS
	02 thru 36	Specify LEAD STYLE from chart below.	—F = Gold flash on post, Matte Tin on tail —L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail —T = Matte Tin	—S = Single Row —D = Double Row	—“XXX” = Stacker Height in inches (0.13 mm) .005" increments Example: —250 = (6.35 mm) .250"	—“XXX” = Polarized Position —A = Alignment Pin (Metal or plastic at Samtec discretion) (4.83 mm) .190" min. board space (—D only) —P = Pick & Place Pad (1.91 mm) .075" min. post height (04-36 only) —TR = Tape & Reel Packaging (—07 lead style not available) (—06 lead style with —P option not available as a standard)	