



Printer TT430

A modern and cost effective
medium volume printer

HellermannTyton



TT430 printer.



TT430 external reel holder (Caddy).

Thermal transfer printer

• TT430

Cutting edge technology, simple to use interface, and a cost-effective solution for printing medium volume labels (around 3,000 a day).

The use of an intuitive touch screen gives quick access to all required print and set-up commands.

The print engine is optimised for consistent high quality printing on all HellermannTyton consumables. The 300 dpi print head is ideally suited for printing high definition graphics such as 2d barcodes, company logos, numbers and text.

Print speeds between 125 mm/s and 30 mm/s ensure you can adjust printing to suit the wide range of consumables on offer. Standard adhesive labels can be printed at 125 mm/s and heatshrink markers at 30 mm/s.



TT430 printer.	
Print Method	Thermal Transfer
Print Head Type	300 dpi, flat type
Print Speed	up to 125 mm/s
Max. Print Width	106 mm
Maximum Print Length	1000 mm
Printer Interfaces	USB 2.0, Ethernet 10/100 Base T
Supported Barcodes, Printer	Standard and 2D
L x H x W	322 mm x 189 mm x 253 mm
Printer Memory	64 MB RAM
Weight	4 kg

Recommended Media

Print on:

- TLFX DS, TDRT DS, TULT DS and ShrinkTrak
- TLFX, TULT, and TCGT continuous tubing
- Tiptags
- Adhesive Labels

www.HellermannTyton.co.uk/TT430



HellermannTyton

HellermannTyton Ltd
Main Contact for Customer Service
Wharf Approach
Aldridge, Walsall, West Midlands
WS9 8BX
Tel: +44 1922 458 151
Fax: +44 1922 743 237
E-Mail: info@HellermannTyton.co.uk
www.HellermannTyton.co.uk

Thermal transfer print technology is ideally suited for printing high quality barcodes, graphics, and text

Technical Table

Article-No.	Type
556-00450	TT430
556-00451	TT430 Caddy
556-00452	S430 Cutter