


Pin Contacts

**Pin 0.63 x 0.63 mm,
Mates with
Micro Quadlok**



Standard Pin Contacts

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish	Part Numbers				Applicator	Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose-Piece	Packaging Unit		
0.14–0.22	–	0.9–1.2	tin plated	1355719-1	13,000	1355720-1	500	541695	–
			gold plated	1355719-2	13,000	1355720-2	500		
0.2–0.5	–	0.9–1.6	tin plated	1-928918-1	13,000	1-963725-1	500	878439	539682-2
			gold plated	1-928918-2	13,000	2-963725-1	500		
0.50–0.75	–	1.6–1.9	tin plated	963716-1	10,000	963730-1	500	878591	539682-2
			gold plated	963716-2	10,000	963730-2	500		

Single Wire Sealing System

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish	Part Numbers				Applicator	Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose-Piece	Packaging Unit		
0.2–0.5	–	0.9–1.6	tin plated	962886-1	10,000	963728-1	500	878553	539685-2
			gold plated	962886-2	10,000	963728-2	500		
0.50–0.75	–	1.6–1.9	tin plated	965908-1	10,000	965909-1	500	878799	539685-2
			gold plated	965908-2	10,000	965909-2	500		

MQS Flexible Flat Cable (FFC) Pin Contacts

Wire Size Range* (mm ²)	Insulation Diameter*		Material and Finish	Part Numbers				Applicator	Hand Tool
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose-Piece	Packaging Unit		
–	–	–	pre-tin plated	1452128-1	13,000	1452129-1	500	–	90273-5

*) Depending on Foil.