



PART NAME	SERIES 2000 UPRIGHT CABINET RACK	PART No.	E-2000	TD	E-2015	REV. DATE	1-2-02
-----------	----------------------------------	----------	--------	----	--------	-----------	--------


FINISH
FRAME ASSEMBLY, SIDES,
DOOR & TOP COVER _____ GRAY TEXTURE OR
ROYAL BLUE TEXTURE
PANEL MOUNTING RAILS _____ SMOOTH BLACK
FRONT TOP TRIM _____ METALLIC GRAY

MATERIAL:
PANEL MOUNTING RAILS _____ 12 GA. STEEL
FRAME TOP, BASE ASSEMBLY,
FILLERS & VERTICAL RAILS _____ 14 GA. STEEL
RAIL SUPPORTS _____ 16 GA. STEEL
TOP COVER & SIDES _____ 18 GA. STEEL
DOOR & FRONT TOP TRIM _____ 20 GA. STEEL



TOP VIEW
(LESS TOP COVER
& FRONT TOP TRIM)

TOP VIEW



REAR VIEW

LEFT SIDE VIEW
(4) PLACES

FRONT VIEW


SECTION 'A-A'
(LESS PANEL MTG. RAILS)

PANEL MOUNTING RAILS (FRONT & REAR)
ARE TAPPED #10-32 ON E.I.A. UNIVERSAL
SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR MOUNTING RC-7758 CASTERS.

LOAD RATING: 1200 LBS. MAX.

* DISCONTINUED



BOTTOM VIEW

PART No.	P.S.	A	B	C	D	E	F	G	H	J	K	L	M
E-2000	21.000	30.250	23.875	20.500	17.000	29.000	27.500	18.937	—	—	—	—	—
* E-2001	31.500	40.750	—	—	—	39.500	38.000	29.437	—	—	—	—	—
* E-2002	35.000	44.250	—	—	—	43.000	41.500	32.937	—	—	—	—	—
E-2003	42.000	51.250	—	—	—	50.000	48.500	—	19.281	17.906	—	—	—
E-2004	52.500	61.750	—	—	—	60.500	59.000	—	24.531	23.156	—	—	—
E-2005	61.250	70.500	—	—	—	69.250	67.750	—	28.906	27.531	—	—	—
E-2006	70.000	79.250	—	—	—	78.000	76.500	—	33.281	31.906	—	—	—
E-2007	78.750	88.000	23.875	20.500	17.000	86.750	85.250	—	—	—	25.125	22.312	23.750
E-2008	21.000	30.250	27.375	24.000	20.500	29.000	27.500	18.937	—	—	—	—	—
* E-2009	31.500	40.750	—	—	—	39.500	38.000	29.437	—	—	—	—	—
* E-2010	35.000	44.250	—	—	—	43.000	41.500	32.937	—	—	—	—	—
E-2011	42.000	51.250	—	—	—	50.000	48.500	—	19.281	17.906	—	—	—
E-2012	52.500	61.750	—	—	—	60.500	59.000	—	24.531	23.156	—	—	—
E-2013	61.250	70.500	—	—	—	69.250	67.750	—	28.906	27.531	—	—	—
E-2014	70.000	79.250	—	—	—	78.000	76.500	—	33.281	31.906	—	—	—
E-2015	78.750	88.000	27.375	24.000	20.500	86.750	85.250	—	—	—	25.125	22.312	23.750