

Products

Product On-Line Catalog

[Product Search](#)

Evaluate

- [FAQ's](#)

Design a Solution

- [Part Draw ings](#)

- [PDF-Adhesive Bac ..](#)

How to Buy

- [Bill of Material](#)

- [Favorite Products List](#)

- [Locate Distributor](#)

[Home](#) > [Product On-Line Catalog](#) > [Product Search](#) >

Current refinements (click  to remove) [Search Tips](#) 

[Part Number](#) > **ABMM-AT-D0**

Your search criteria matched only one product, shown below

ABMM-AT-D0



- Superior adhesive for long term reliability
 - 2-up mount configuration speeds liner removal and installation
 - 4-way cable tie entry makes part orientation fast and easy
 - Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
 - Use with Panduit cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Cable Ties.

■ Part Number	ABMM-AT-D0
■ RoHS Compliancy Status	Compliant
■ Part Description	4-Way Adhesive Backed Cable Tie Mount
■ Product Type	Cable Tie Mounts - Adhesive Backed
■ Material	Weather Resistant ABS
■ Color	Black
■ UL Recognized	E136577
■ Height (In.)	0.18
■ Height (mm)	4.6
■ Length (In.)	0.75
■ Length (mm)	19.1
■ Width (In.)	0.75
■ Width (mm)	19.1
■ Adhesive Type	Acrylic
■ CE Compliant	Yes
■ Environment	Outdoor/High Temp
■ Max. Bundle Diameter (mm)	3.7
■ Max. Continuous Use Temperature	180°F (82°C)
■ Max. Static Load (g)	136
■ Max. Static Load (Lbs.)	0.30
■ Mounting Method	Acrylic Adhesive Tape
■ Pricing Description	Cable Tie Mount, Hi Tmp. Adh., .75"x.75" (19.1mm x 19.1mm), WR BL
■ Temperature Range	180°F (82°C)
■ Type	Adhesive Backed
■ Used With Cable Ties	M, I
■ Min. Order UOM	PC
■ Min. Order Qty.	500
■ BOM Qty. (# of Pkgs.)	0
■ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.