






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/16/02	MCCORMICK
B	ECN# 1605 ADDED COMPONENT SPECIFICATIONS	12/09/03	MCCORMICK
C	ECN# 2082 CORRECTING DIM LENGTH	05/24/05	M.LAHEY



2X TYPE 1 JACK

TABLE	
J1	J2
PIN 1	PIN 1
PIN 2	PIN 2
PIN 3	PIN 5
PIN 4	PIN 6
PIN 5	PIN 3
PIN 6	PIN 4
SHELL	SHELL



Component Specifications	
Material	
Housing	ABS 94V-0 Rating
Connector	Plastic; PBT with Glass Fiber
Contact	Brass
Shell	Brass
PCB	Epoxy Glass FP-4 94V-0 Rating
Finish	
Housing	Chrome
Contact	Gold 30 Micro Inch
Shell	Nickel
Electrical	
Current Rating	2 AMP Max
Voltage Rating	140 VDC
Environmental	
Operating Temperature	-20°C to +80°C

C's-132

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X ±.1
XX ±.05
XXX ±.005
CABLE LENGTH TOLERANCE
≤300' ±5% >300' ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/13/2002
CHECKED BY D.PARHAM	01/13/2002
APPROVED BY R.CARRICK	01/13/2002

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION COUPLER PANEL MOUNTED FIREWIRE1/1 SHIELDED			
DRAWING TITLE OUTLINE DRAWING			
SIZE A	FSCM NO. 43321	DWG. NO. ECF504-94MS-OD1	REV. C
SCALE: NONE		CAD FILE: ECF504-94MS-OD1.SLDDRW	SHEET 1 OF 1