


Cable Ties/High Temperature Ties

HellermannTyton's high temperature cable ties provide excellent resistance in operating temperatures up to 275°F (135°C), while still maintaining tensile strength properties.



Material Data	
Material	Polyamide 4.6 (PA46)
Operating Temperature	-40 °F to +275 °F (-40 °C to +135 °C) continuous
Flammability	UL94 V2



Product Selection		Type	Min. Tensile Strength	Length (L)		Max Ø Bundle	Width (W)		Color	Pkg. Qty.
Article No.	Part No.		lbs. (N)	in.	(mm)	in. (mm)	in.	(mm)		
116-01811	T18R1STNLM5	T18R1STNLM5	18 lbs. (80)	4"	(100)	.87" (22)	.10"	(2.5)	Brown	100
116-03011	T30R1STNLM4	T30R1STNLM4	30 lbs. (135)	5.9"	(150)	1.38" (35)	.14"	(3.5)	Brown	100
116-05011	T50R1STNLM5	T50R1STNLM5	50 lbs. (225)	7.9"	(200)	1.97" (50)	.18"	(4.6)	Brown	100
111-05443	T50L1STNLM4	T50L1STNLM4	50 lbs. (225)	15.3"	(390)	4.33" (110)	.18"	(4.6)	Brown	100