


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs. / 100 pcs. (g)	RECOMMENDED TOOL SETTING
	MIN. in (mm)	MAX. in (mm)											
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	11 (49)	MINIATURE	CURVED	.06 (27)	GS2B MIN 2
PLT1.5I	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	18 (80)	INTERMEDIATE	CURVED	.10 (46)	GS2B INT 3
PLT2S	.06 (1.5)	1.88 (48)	.052 (1.3)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	7.4 (188)	30 (133)	STANDARD	CURVED	.23 (104)	GS2B STD 5
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	30 (133)	STANDARD	CURVED	.35 (139)	GS2B STD 5
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	30 (133)	STANDARD	CURVED	.43 (195)	GS2B STD 5
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	8.1 (206)	50 (222)	HEAVY	STRAIGHT	.61 (277)	GS4H HVY 5
PLT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	11.4 (290)	50 (222)	HEAVY	STRAIGHT	.79 (359)	GS4H HVY 5
PLT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.320 (8.1)	.290 (7.4)	.480 (12.2)	14.5 (368)	50 (222)	HEAVY	STRAIGHT	1.0 (454)	GS4H HVY 5

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) MATERIAL SUFFIX CODE: -100=WEATHER RESISTANT BLACK
-109=PANDUIT STANDARD POLYPROPYLENE
IS OFF-SHADE GREEN

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

SS_15356_10.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES
PLT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.1(2.5) (.XXX) ±.010(.25)
(.XX) ±.20(.5) ANGLES ±-----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
CEW

MAT'L:

SCALE
NONE

DATE
1-22-85

POLYPROPYLENE

DRAWING NO.

SS-15356

DWG
A
SIZE

10	9/9/04	ERW		CORRECTED METRIC CONVERSIONS	15356	10							
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP					