




Model Number:	55-2953	
GENERAL SPECIFICATIONS		
Nominal Diameter:	15 inch	
Rated Impedance:	8 ohms	
Operating Bandwidth:	32Hz ~ 2KHz	
Power Handling Capacity:	200W RMS	
Sensitivity (1W/M):	98 dB	
Voice Coil Diameter:	3 inch	
THIELE-SMALL PARAMETER		
Resonance Frequency	Fs:	32 Hz
DC Resistance	Re:	7.2 ohm
Mechanical Q Factor	Qms:	2.9
Electrical Q Factor	Qes:	0.475
Total Q Factor	Qts:	0.41
Equivalent Cas air load	Vas:	232 liters
Coil Inductance	Le:	1.37 mH
Efficiency Bandwidth Product	EBP	67.37
Voice Coil Over Hang	X-max	3.75mm
PHYSICAL INFORMATION		
Basket:	Stamped Steel	
Magnet Type:	67 OZ	
Cone Material:	None press paper	
Surround:	cloth	
Dust Cap:	paper	
Damper:	cloth	





ALL DIMENSIONS ARE IN MILLIMETERS