





NOTES:

1. HARDWARE IS INCLUDED
2. SUGGESTED MTG. HOLE .228 DIA.


LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	3000 pF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 350 VDC MAX. 125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	---
10	5
100	45
1 GHz	70
10 GHz	--

SCHEMATIC



MARKING:

PART:
SCI 1201-052
BAG:
1201-052
DATE CODE
QTY./BAG
(100/ BAG MAX.)

	6	5	4	3	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED		 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA
	CN 202459	CN 200613	CN 193706	CN 185003 REDRAWN	CHANGE NOTICE				
						Fractions ± 1/64		Dwn. KAUFFMAN	Description
						Dec. .xx±		Ckd. 7/10/01	FILTER, SING, Pi, BSHG
						Dec. .xxx± .010			
						Angles ±0° 30'			
						CODE IDENT. NO. DLSP2		Scale NONE	1201-052