

► [Heatsinks f.cool](#)

► [Cases f.case](#)

▼ [Connectors f.con](#)

► [Sockets](#)

▼ [PCB connectors](#)

■ [Male headers](#)

■ [Female headers](#)

■ [Direct female connector](#)

■ [Jumpers](#)

► [IDC-connectors](#)

► [D-Sub connectors](#)

■ [Brackets for PC](#)


► [Optoelectronics](#)

Female headers

BL 8 26

for square 0.635 mm and up to 0.85 mm Ø, packing (option) bar magazine

add to request



Features

Technical Drawing

Accessories / related products

no. of contacts	26
contact material	CuZn-alloy
contact sleeve	tin-plated
surface contact / contact sleeve	Ni+4...6µm Sn
contact spring	gold-plated
inner contact spring material	CuBe-alloy
inner contact spring surface	
Typ Innenfeder	
plugability	
Einstecktiefe	
plug-in cross-section	square 0.635 Ø 0.65 to 0.85
insertion / extraction force	
shock resistance	50 g
vibration resistance max.	15 g
volume resistivity	
capacity between two adjacent contacts	≤ 0,3 pF
nominal current	3 A
nominal voltage	
test voltage	1500 V
material isolation body	
temperature range	
class of flammability	UL 94 V-0
insulation resistance	
version	standard
connection type	soldering
reflow solderable	yes