

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200980203

Status:

Active

Overview:

PROFIBUS Solutions

Description:

PROFIBUS 90° Female/Male D-Sub Connector to Pigtail, With Programming Port, 22 AWG, PUR Cable, 1.0m (3.28') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                              |
|-------------------------------|----------------------------------------------|
| General                       |                                              |
| Product Family                | Industrial Cordsets                          |
| Series                        | 120098                                       |
| Comments                      | With Programming Port, With Programming Port |
| Connector End A               | D-Sub (9-pin)                                |
| Connector End B               | Pigtail                                      |
| IP Rating                     | IP67                                         |
| Material - Contact            | N/A                                          |
| Overview                      | PROFIBUS Solutions                           |
| Product Name                  | PROFIBUS                                     |
| Protocol                      | N/A                                          |
| Region                        | America, Asia, Europe                        |
| Type                          | Single Ended                                 |
| UPC                           | 78172504509                                  |
| Physical                      |                                              |
| Cable Diameter                | 8.00mm (.315")                               |
| Cable Length                  | 1.0m (3.28')                                 |
| Color - Cable Jacket          | Purple                                       |
| Coupling Style                | Threaded                                     |
| Gender                        | Female/Male to Pigtail                       |
| Keyway                        | None                                         |
| LED Indicator                 | No                                           |
| Material - Cable Jacket       | PUR                                          |
| Material - Connector Body     | PUR                                          |
| Material - Coupling Nut       | Gray Anodized Aluminum                       |
| Material - Plating Mating     | N/A                                          |
| Orientation                   | 90°/90° to Pigtail                           |
| Poles                         | N/A                                          |
| Temperature Range - Operating | 0°C to +60°C                                 |
| Wire Size AWG                 | N/A                                          |
| Wire/Cable Type               | Shielded-Twisted Pair                        |
| Electrical                    |                                              |
| Current - Maximum per Contact | 4.0A                                         |
| Voltage - Maximum             | 250V AC/DC                                   |
| Material Info                 |                                              |
| Engineering Number            | P03S07PP4M010                                |
| Reference - Drawing Numbers   |                                              |
| Sales Drawing                 | SD-120098-029                                |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

120098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION