




TW-20-07-T-D-550-SM

TW-10-04-L-D-300-SM

TW SERIES

SMT BOARD STACKERS



Available
with optional
alignment pins

TW — **NO. PINS PER ROW** — **LEAD STYLE** — **PLATING OPTION** — **ROW OPTION** — **STACKER HEIGHT** — **SM** — **OTHER OPTIONS**

02 thru 36

**Specify
LEAD
STYLE
from
chart
below.**

-F
Gold flash
on post,
Matte Tin
on tail

-L
= 10 μ"
(0.25 μm)
Gold on post,
Matte Tin
on tail

-T
Matte Tin

-S
= Single
Row

-D
= Double


— “XXX”
= Stacker
Height
in inches
(0.13 mm)
.005"
increments
Example:
-250
= (6.35 mm)
.250"

–“XXX”
= Polarized Position

-A
= Alignment Pin
(Metal or plastic
at Samtec discretion)
(4.83 mm) .190" min.
board space
(-D only)



-P
= Pick & Place Pad
(1.91 mm) .075" min.
post height
(04-36 only)

-TR
= Tape & Reel
Packaging
(-07 lead style
not available)
(-06 lead style with
-P option not available
as a standard)



LEAD STYLE	OAL
-02	(7.85) .309
-03	(11.86) .467
-04	(12.37) .487
-06	(15.37) .605
-07	(17.35) .683
-09	(9.86) .388

ROW OPTION	A
—S	(5.08) .200
—D	(6.35) .250



Due to technical progress, all designs, specifications and components are subject to change without notice.