



Dimensions: mm (In)

**Electrical Specifications:**

- Rating: 6A/125VAC, 3A/250VAC
- Contact Resistance: 20mΩ or less @ 2.5VDC and 1A
- Insulation Resistance: 100MΩ @ 500VDC
- Dielectric Strength: 1,000VAC, 50/60 Hz for 1 minute
- Electrical Life: 5,000 Cycles

Mechanical Specifications:

- Circuit: 3P SPDT ON-OFF-ON
- Mechanical Life: 30,000 Cycles

Materials:

- Layer: chrome plated brass
- Bushing: nickel plated brass
- Plate: nickel plated brass
- Cover plate: stainless steel
- Case: molded melamine-phenolic
- Terminals: copper sheet with gold flash

Miniature Toggle Switch
10TF235

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10TF235](#)