






DESCRIPTION: (CPAD850) N(F-F) SPLICE UG-29B/U
 MODEL NUMBER: 26-8010
 APPLICATION: ADAPTER
 CRIMP TOOL: N/A
 IMPEDANCE: N/A
 FREQUENCY RANGE: N/A
 MATERIAL: BODY BRASS NICKEL PLATED
 INSULATOR POM
 CONTACT BRASS NICKEL PLATED
 RoHS COMPLIANCE: YES
 TECHNICAL DETAIL: REFER TO CINCH DOCUMENT P/N 26-0000



 <p>cinch connectivity solutions a bel gong group</p>	3RD ANGLE PROJECTION 	AIM-Cambridge		
	RoHS2 <input checked="" type="checkbox"/> 2011/65/EU	Title: (CPAD850) Type N (Jack/Jack) Splice, UG/29B/U, Adapter		
	UNLESS OTHERWISE SPECIFIED UNITS: METRIC X ±.3 XX ±.10 ANGLES ±2°	Model No. 26-8010		
	INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	Size A	DO NOT SCALE DRAWING	Date: 2015/6/24