

Die-set - SDE (shoulder)

Predominately used on closed-barrel terminals.

These Dies are ideally suited to R&D prototyping, networking, commercial & industrial and all manor of maintenace applications.

Image representative of type only

Features:

Use in:

SDE PRO-CRIMPER III Hand Tool 354940-1

SDE SA Hand Tool 9-1478240-0

SDE DA Hand Tool 1213745-1

SDE BT 3500 Battery-Hydraulic Hand Tools:

2-2031400-1 - EMEA or 3-2031400-1 - UK

+ SDE Head 2031450-1

SDE 626 Head 679304-1 + accessories

SDE Electric Terminator 1490076-2

SDE Bench Press AT-SC 528050-1



Part Number	Description	mm ² (AWG) or other
58436-2	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Hex; 2.54 (.100), 8.23 (.324), 1.73 (.068)
58436-3	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Hex; 2.54 (.100), 8.23 (.324), 1.73 (.068)
58436-1	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Hex; 5.41 (.213), 6.48 (.255), 1.73 (.068)
58425-2	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Sqre; 1.07 (.042). Hex; 3.25 (.128), 4.52 (.178)
58425-3	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Sqre; 1.07 (.042). Hex; 3.84 (.151), 8.23 (.324)
58425-1	75-Ohm Hex Crimp BNC and TNC plug connectors	mm (") Sqre; 1.07 (.042). Hex; 5.41 (.213), 6.48 (.255)
58509-1	BUDGET SOLISTRAND	0.4 - 6.0 [22-10]
58573-2	Spare Wire Cap	0.15 - 6.0 [26-10]
91902-1	Coax - N Series	RG 141
58485-1	Coax - Hex COMMercial	RG, 8,9,11,213,214,216
58560-2	MODULAR PLUG connectors	10 Posn
790163-6	MODULAR PLUG - 8 Posn	
790163-4	MODULAR PLUG - 8 Posn Shielded	CAT 6 5.40 hex 5.6 lg
224928-2	MODULAR PLUG - 8 Posn, strain relief	Ø4.70 - 5.76 Ins. Ø0.19-0.22mm
790163-2	Modular Plug 8 Position Shielded	0.15 - 0.2 [26-24] CAT 6
91911-3	MULTI-MATE - Submin	RG 174
58424-1	Optimate ST	Cable Dia 3 mm
58423-1	PIDG, PLASTI-GRIP - RBY All Types including PIDG FASTON Flag 22-18 & 16-14	0.4 - 6.0 [22-10]
1424050-1	RF Coax - BNC DUAL CRIMP 50ohm	see Cat. 1301719
58536-1	Coax	see Cat. 1307191
58545-1	SOLISTRAND Terminals & Splices	0.4 - 6.0 [22-10]

Die-set - SDE (pin)

Predominately used on open-barrel terminals.

These Dies are ideally suited to R&D prototyping, networking, commercial & industrial and all manor of maintenace applications.

Image representative of type only

Features:

Use in:

SDE PRO-CRIMPER III Hand Tool 354940-1

SDE SA Hand Tool 9-1478240-0

SDE DA Hand Tool 1213745-1

SDE BT 3500 Battery-Hydraulic Hand Tools:

2-2031400-1 - EMEA or 3-2031400-1 - UK

+ SDE Head 2031460-1

SDE 626 Head 679304-1 + accessories

SDE Electric Terminator 1490076-2

SDE Bench Press AT-SC 528050-1



Part Number	Description	mm² (AWG) or other
91387-2	4.2 PE series	0.15 - 0.4 [26-22]
91388-2	4.2 PE Series	0.4 - 1.0 [22-18]
1891358-1	AMP EI Receptacle	0.15 - 0.6 [26-20]
58641-2	AMP MOD IV, V	0.15 - 0.4 [26-22]
58448-3	AMPLIMITE HD-20	[28-20]
90800-2	AMPLIMITE HD-22	0.08 - 0.4 [28-22]
217212-2	Closed End Splice	1.0 - 6.0 [18-10]
90872-2	COMM 0.93 mm	0.2 - 1.0 [24-18]
90574-2	Commercial MATE-N-LOK	0.2 - 0.96 [24-18]
90575-2	Commercial MATE-N-LOK	0.6 - 2.5 [20-14]
58517-2	CST-100	0.15 - 0.4 [26-22]
58548-2	EI Receptacle	0.15 - 0.6 [26-20]
58652-2	FASTON 2.8 (.110) Receptacle	0.6 - 1.5 [20-16]
58524-2	FASTON 6.3 [.250] Receptacle	1.0 - 2.5 [18-14]
91304-2	Junior Power TIMER 2.8 (SWS) & Micro TIMER	0.5 - 1.0 [20-18]
58603-2	Junior Power TIMER; TAB 2.8	0.75 - 2.5 [20-14]
1752938-2	MATE-N-LOK 3.5 (.140)	0.75 - 1.64 [18-16]
90760-2	Mini Universal MATE-N-LOK	[20-16]
90759-2	Mini Universal MATE-N-LOK	[22-18]
90758-2	Mini Universal MATE-N-LOK	0.15 - 0.4 [26-22]
58707-2	Mini-Universal MATE-N-LOK	0.6 - 1.5 [20-16]
58522-2	MULTILOCK 040	0.4 - 0.6 [22-20]
90652-2	MULTILOCK 040 MkII	0.4 - 1.0 [22-18]
90653-2	MULTILOCK 070	0.4 - 0.6 [22-20]
58606-2	Pin/Socket Ø1.5 & Ø2.5 (SWS)	1.0 - 2.5 [18-14]
58593-2	Power Quadlock	1.5 - 3.0 [16-14]
58594-2	Power Quadlock	4.0 [12]
58595-2	Power Quadlock (SWS)	1.5 - 2.5 [16-14]
58596-2	Power Quadlock (SWS)	4.0 [12]
58614-2	SL 156	0.2 - 0.96 [24-18]
58583-2	SUPERSEAL 1.5 series	0.5 - 1.0 [20-18]
58495-2	TYPE III+; TYPE VI	0.08 - 1.5 [28-16]
58628-2	ULTRA FAST (excluding Flag Terminals)	0.15 - 2.5 [26-14]
58630-2	ULTRA FAST	4.0 - 6.0 [12-10]
90546-2	Universal MATE-N-LOK	0.5 - 2.1 [20-14] Ins. Ø1.53-3.30 mm
90547-2	Universal MATE-N-LOK	0.5 - 2.1 [20-14] Ins. Ø3.30-5.08mm

SDE PRO-CRIMPER III

354940-1 - Base Tool without Die-set

An alternative to SDE PEW 12 & SDE DA hand tools, but with different features and a different geometry

Image representative of type only

Features:

Accepts all SDE Shoulder & Pin Dies

Ratchet mechanism ensures complete crimp cycle

Emergency ratchet release feature

Ergonomic non-slip handles

Approximate weight 0.59 kg (1.3 lbs)



Part Number	Description	mm ² (AWG) or other
58448-2	AMPLIMITE HD-20	[28-20]
90800-1	AMPLIMITE HD-22	0.08 - 0.4 [28-22]
90760-1	Mini Universal MATE-N-LOK	[20-16]
90759-1	Mini Universal MATE-N-LOK	[22-18]
790163-3	MODULAR PLUG - 8 Posn Shielded	CAT 6 5.40 hex 5.6 lg
790163-1	Modular Plug 8 Position Shielded	0.15 - 0.2 [26-24]
90652-1	MULTILOCK 040 MkII	0.4 - 1.0 [22-18]
58433-3	PIDG, PLASTI-GRIP - RBY All Types including PIDG FASTON Flag 22-18 & 16-14	0.4 - 6.0 [22-10]
58593-1	Power Quadlock	1.5 - 3.0 [16-14]
58594-1	Power Quadlock	4.0 [12]
58595-1	Power Quadlock (SWS)	1.5 - 2.5 [16-14]
58596-1	Power Quadlock (SWS)	4.0 [12]
58546-1	SOLISTRAND Terminals & Splices	0.4 - 6.0 [22-10]
58546-2	SOLISTRAND Terminals & Splices	0.4 - 6.0 [22-10]

Die-set - SDE SA

These dies can have up to five crimp positions and are NOT suitable for use in the SDE Procrimper III Hand Tool

Image representative of type only

Features:

Use in:

SDE SA Hand Tool 9-1478240-0

SDE BT 3500 Battery-Hydraulic Hand Tools:

2-2031400-1 - EMEA or 3-2031400-1 - UK

+ SDE Head 2031450-1

SDE 626 Head 679304-1 + accessories

SDE Electric Terminator 1490076-2

SDE Bench Press AT-SC 528050-1

(not for use in SDE PRO-CRIMPER III Hand Tool 354940-1)



Part Number	Description	mm ² (AWG) or other
9-1478247-0	Coax - GREENPAR	BT2003
9-1478243-0	Coax - GREENPAR	PSF 1/2M, Belden 8281, TM 3205
9-1478248-0	Coax - GREENPAR	RG 174, 178, 188... See 408-8698
9-1478245-0	Coax - GREENPAR	RG 174, 179, 187... see 408-8694
9-1478242-0	Coax - GREENPAR	RG 55, 58, 59, 62... see 408-8694
9-1478246-0	Coax - GREENPAR	RG 9, 58, 141... see 408-8694
2063583-2	HTS: HE/HA; HN D; HVT Contacts	0.14 - 4.0
2063041-2	Micro Quadlok	0.25 - 0.5 [24-22]
2063030-1	PIDG, PLASTI-GRIP Terminals & Splices with Terminal Locator	0.4 - 6.0 [22-10]
2031973-2	Universal MATE-N-LOK	0.2 - 2.0 Ins. Ø1.0-3.3mm
2063379-2	Universal MATE-N-LOK	0.5 - 2.0 Ins. Ø1.4-2.4mm

SDE SA

9-1478240-0 - Base Tool without Die-set

An alternative to PRO-CRIMPER III & SDE DA hand tools, but with different features and a different geometry

Image representative of type only

Features:

Accepts all SDE; Shoulder, Pin & Plus Dies

Ratchet mechanism ensures complete crimp cycle

Virtually a straight action jaw closure

Easy access ratchet release

Handle pressure adjustment with locking device

Ergonomic non-slip handles

Approximate weight 0.59 kg (1.3 lbs)



Part Number	Description	mm ² (AWG) or other
9-1478239-0	Coax - GREENPAR	RG 8, 213... See 408-8695
2063583-1	HTS: HE/HA; HN D; HVT Contacts	0.14 - 4.0
1752938-1	MATE-N-LOK 3.5 (.140)	0.75 - 1.64 [18-16]
91391-1	Micro MATE-N-LOK	0.06 - 0.5 [30-20]
2063041-1	Micro Quadlok	0.25 - 0.5 [24-22]
2031973-1	Universal MATE-N-LOK	0.2 - 2.0 Ins. Ø1.0-3.3mm
2063379-1	Universal MATE-N-LOK	0.5 - 2.0 Ins. Ø1.4-2.4mm

Die-set - SDE Premium

These dies are based on the Double Action Hand Tools used in Aerospace & Military applications.

Image representative of type only

Features:

Insulation crimp height adjustment
Terminal locator & wire stop

Use in:

SDE BT 3500 Battery-Hydraulic Hand Tools:
2-2031400-1 - EMEA or 3-2031400-1 - UK
+ SDE Head 2031460-1
SDE Electric Terminator 1490076-2



Note: The Specifications shown against the Dies listed are only applicable when using terminals and wires recommended for the relevant industry

Part Number	Description	mm ² (AWG) or other
91964-2	PIDG, PLASTI-GRIP Terminals & Splices - equivalent crimp to 47386 Qualified; Mil-T-7928; LUL RSE 024 pt6 & EE6161 Marks the applied product with a two dot indent code.	0.4 - 1.5 [22-16]
91963-2	PIDG, PLASTI-GRIP Terminals & Splices - equivalent crimp to 47387 Qualified; Mil-T-7928; LUL RSE 024 pt6 & EE6161 Marks the applied product with a two dot indent code.	1.5 - 2.5 [16-14] □ 0.6 - 1.5 [20-16] HD
91965-2	PIDG, PLASTI-GRIP Terminals & Splices - equivalent crimp to 59239-4 Qualified; Mil-T-7928; LUL RSE 024 pt6 & EE6161 Marks the applied product with a two dot indent code.	4.0 - 6.0 [12-10]

SDE 626 Pneumatic

Ideal for low to medium production volumes.

Image representative of type only

Features:

Accepts any Pin / Shoulder SDE Die-sets
All pneumatic

Includes:

Head 679304-1
Tool Holder with Ratchet 356302-1
Hand held power unit 189721-1

Option to convert to Bench mount:

Bench-mount 856402-1
Foot Actuated Power Unit 189722-1



for more 626 options please see the Power Assist section

Part Number	Description	mm ² (AWG) or other
1213855-1	SDE 626 Pneumatic for SDE Pin & Shoulder dies	4.0 - 6.0 [12-10]

SDE Electric Terminator

1490076-2 - Portable Bench-top Unit with SDE Head & Foot Switch

Features:

Ideal for low to medium production volumes.

Accepts any SDE Die-set

Mains powered unit - no air required

Switchable 110v or 240v supply

Cycle Counter

Two stage crimp cycle option

for other SDE Power Options please see the Power Assist section

Image representative of type only



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1213745-1](#)