

SPECIFICATIONS





| PARAMETERS | VALUES | UNITS |
|--------------------------|-------------------|-------|
| RESONANT FREQUENCY | $2,900 \pm 500$ | Hz |
| RESONANT IMPEDANCE (MAX) | 500 | Ohm |
| MAX INPUT VOLTAGE | 30 | Vp-p |
| CAPACITANCE @ 1kHz | $25,000 \pm 30\%$ | pF |
| PLATE MATERIAL | BRASS | - |
| OPERATING TEMPERATURE | $-20 \sim +70$ | °C |
| STORAGE TEMPERATURE | $-30 \sim +80$ | °C |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO
PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED,
INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY

| LTR | DESCRIPTION | DATE | APPROVED |
|-----|--|-----------|----------|
| - | RELEASED FROM ENGINEERING | 4/11/2002 | |
| A | REVISED TO NEW TEMPLATE | 9/4/2003 | R.W. |
| B | REVISED SPECIFICATIONS | 1/15/2004 | R.W. |
| C | REVISED DIMENSION SIZE AND STYLE | 1/25/2006 | B.R. |
| D | REVISED TO INVENTOR 3-D DRAWING TEMPLATE | 8/26/2010 | B.R. |
| E | REVISED THICKNESS AND CERAMIC DIAMETER | 5/3/2011 | B.R. |



A (12 : 1)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE
SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS,
TOLERANCES
ARE ±0.5 AND
ANGLES ARE ±3°.

SIZE
A3

AB3529BF.idw

 pui
audio™ inc
a projects unlimited company

AB3529BF

Bender

Edition
-
Sheet
1 / 1

| Designed by | Date | Checked by | Date | Approved by | Date | Drawn Date |
|-------------|-----------|------------|------|-------------|-----------|------------|
| RABL | 4/11/2002 | | | S.J. | 4/12/2002 | 8/26/2010 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AB3529BF](#)