



AC Compact Fan Kits

Kits incorporating a range of AC fans, a power lead and either a metal guard or an air filter option.

- 230V fans
- Can be operated at 50 or 60Hz
- Metal fan housings
- IP20 Protection
- Lead 610mm
- Filter pads that can be changed without switching off the fan

Part Number	Airflow		Voltage	Noise	Bearings	Power	Speed	Temperature Range	Length	Width	Depth	Fan Type	Lead	Guard	Filter
	M3/h	CFM													
9956L-KR0	84	49.4	230	29	BB	9.5	1850	-40...+80	119	119	25	9956L	LZ120/1.5	LZ30K	-
9956L-KR1	84	49.4	230	29	BB	9.5	1850	-40...+80	119	119	25	9956L	LZ120/1.5	-	PMFA120T
9956-KR0	117	68.9	230	37	BB	14.0	2450	-40...+70	119	119	25	9956	LZ120/1.5	LZ30K	-
9956-KR1	117	68.9	230	37	BB	14.0	2450	-40...+70	119	119	25	9956	LZ120/1.5	-	PMFA120T
4890N-KR0	80	47.1	230	25	SB	11.0	1550	-10...+70	119	119	38	4890N	LZ120/1.5	LZ30K	-
4890N-KR1	80	47.1	230	25	SB	11.0	1550	-10...+70	119	119	38	4890N	LZ120/1.5	-	PMFA120T
4850N-KR0	100	58.9	230	32	SB	10.0	1800	-10...+70	119	119	38	4850N	LZ120/1.5	LZ30K	-
4850N-KR1	100	58.9	230	32	SB	10.0	1800	-10...+70	119	119	38	4850N	LZ120/1.5	-	PMFA120T
4650N-KR0	160	94.2	230	46	SB	19.0	2650	-10...+55	119	119	38	4650N	LZ120/1.5	LZ30K	-
4650N-KR1	160	94.2	230	46	SB	19.0	2650	-10...+55	119	119	38	4650N	LZ120/1.5	-	PMFA120T
4656N-KR0	160	94.2	230	47	BB	19.0	2650	-40...+85	119	119	38	4656N	LZ120/1.5	LZ30K	-
4656N-KR1	160	94.2	230	47	BB	19.0	2650	-40...+85	119	119	38	4656N	LZ120/1.5	-	PMFA120T
4600N-KR0	180	105.9	115	50	SB	18.0	3100	-10...+60	119	119	38	4600N	LZ120/1.5	LZ30K	-
4600N-KR1	180	105.9	115	50	SB	18.0	3100	-10...+60	119	119	38	4600N	LZ120/1.5	-	PMFA120T
4606N-KR0	160	94.2	115	46	SB	19.0	2650	-10...+55	119	119	38	4606N	LZ120/1.5	LZ30K	-
4606N-KR1	160	94.2	115	46	SB	19.0	2650	-10...+55	119	119	38	4606N	LZ120/1.5	-	PMFA120T
ACI4420HH-KR0	180	105.9	230	42	BB	4.4	3350	-20...+75	119	119	38	ACI4420HH	LZ120/1.5	LZ30K	-
ACI4420HH-KR1	180	105.9	230	42	BB	4.4	3350	-20...+75	119	119	38	ACI4420HH	LZ120/1.5	-	PMFA120T
W2E142-BB01-01-KR0	330	194	230	52	BB	29.0	2800	-25...+55	150	172	38	W2E142-BB01-01	LZ120/1.5	03749-2-4039	-
W2E142-BB01-01-KR1	330	194	230	52	BB	29.0	2800	-25...+55	150	172	38	W2E142-BB01-01	LZ120/1.5	-	PMFA160