



Dimensions: mm (In.)




MOUNTING HOLES


2- $\varnothing 3.1$ ($\varnothing .122$) mounting holes or M3 screw holes.



CONTACT CONFIGURATION






OPERATING CHARACTERISTICS



TERMINAL TYPES

Quick connect terminal 187 series (D)



Electrical Specifications:

- Rating: 16A/125-250VAC
- Insulation Resistance (at 500VDC): 100M Ω Min.
- Dielectric Strength: 1,000VAC RMS(50-60HZ)
- Contact Resistance (Initial): 30m Ω Max.
- Electrical Operating Frequency: 10-30 operations/min.
- Operating Speed: 0.1mm to 1m/sec.
- Electrical Life: 6,000~100,000 operations(Min.)

Mechanical Specifications:

- Mechanical Operating Frequency: 300 operations/min.
- Mechanical Life: 5,000,000 operations(Min.)

Operating Characteristics:

- OF (g) max: 185
- OP (mm): 20.4 $\pm$ 1.4
- PT max: 4.50mm
- OT min (mm): 0.90
- MD max (mm): 2.60

Miniature Snap Switch
SNS73-16-185RR-Q21

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-73-16-185RR-Q21](#)