



Pb Free

RoHS Compliant

Features

- Crystal unit for Consumer Products
- Metal package, leaded type
- A resistance weld hermetic sealed type
- Suitable for high density assembly and mass production

Applications

- Digital Electronics
- Consumer Products
- Car audio and accessories

How to Order

HC49SFNB 03200 □□ □ □ □ □ □

① Series	② Frequency	③ Load Capacitance	④ Frequency Stability	⑤ Operating Temp. Range	⑥ Frequency Temp. Stability	⑦ Individual Specification
H0	12 pF	Std.	P	±50×10 ⁻⁶	Std.	
ES	-10 to +70°C					

Specifications

Item	Symbol	Specification	Units	Remarks
Frequency Range	f _{nom}	3200 to 33999	34 to 60 (MHz)	kHz
Overtone Order	OT	Fundamental	3rd. Overtone	—
Load Capacitance	CL	12	pF	
Frequency Stability	f _{tol}	±50	×10 ⁻⁶	25°C ±3°C
Motional Series Resistance	R1	Table 1	ohm	
Drive Level	DL	Table 2	μW	
Operating Temp. Range	T _{use}	-10 to +70	°C	
Storage Temp. Range	T _{stg}	-40 to +85	°C	
Frequency Temp. Characteristics	f _{tem}	±50	×10 ⁻⁶	Freq. deviation from the value at 25 °C

□ Please contact us for other specifications.

Table1 Motional Series Resistance

Frequency Range	Motional Series Resistance
3200 to 3499kHz	300Ω max.
3500 to 4099kHz	150Ω max.
4100 to 4799kHz	120Ω max.
4800 to 4999kHz	100Ω max.
5000 to 7999kHz	80Ω max.
8000 to 11999kHz	60Ω max.
12000 to 33999kHz	50Ω max.
*34 to 34.9MHz	150Ω max.
*35 to 60MHz	100Ω max.

* 3rd Overtone

Table2 Level of Drive

Frequency Range	Level of Drive
3200 to 15999kHz	10μW (500 μW max.)
16000 to 24999kHz	10μW (300 μW max.)
25000 to 33999kHz	10μW (100 μW max.)
34 to 60MHz	10μW (300 μW max.)

Typical Frequencies and Part Numbers

Frequency (kHz)	Part Number
3200.000	HC49SFNB03200H0PESZ1
3579.545	HC49SFNB03579H0PESZ1
3686.400	HC49SFNB03686H0PESZ1
4000.000	HC49SFNB04000H0PESZ1
4194.304	HC49SFNB04194H0PESZ1
4332.000	HC49SFNB04332H0PESZ1
4433.619	HC49SFNB04433H0PESZ1
4500.000	HC49SFNB04500H0PESZ1
4915.200	HC49SFNB04915H0PESZ1
6000.000	HC49SFNB06000H0PESZ1
6144.000	HC49SFNB06144H0PESZ1
7200.000	HC49SFNB07200H0PESZ1
7372.800	HC49SFNB07372H0PESZ1
8000.000	HC49SFNB08000H0PESZ1
10000.000	HC49SFNB10000H0PESZ1
10738.635	HC49SFNB10738H0PESZ1
11000.000	HC49SFNB11000H0PESZ1
11059.200	HC49SFNB11059H0PESZ1
12000.000	HC49SFNB12000H0PESZ1
12288.000	HC49SFNB12288H0PESZ1
13500.000	HC49SFNB13500H0PESZ1
14318.180	HC49SFNB14318H0PESZ1
16000.000	HC49SFNB16000H0PESZ1
16934.400	HC49SFNB16934H0PESZ1
17280.000	HC49SFNB17280H0PESZ1
17734.476	HC49SFNB17734H0PESZ1
20000.000	HC49SFNB20000H0PESZ1
21477.270	HC49SFNB21477H0PESZ1
24000.000	HC49SFNB24000H0PESZ1
24576.000	HC49SFNB24576H0PESZ1
25000.000	HC49SFNB25000H0PESZ1
27000.000	HC49SFNB27000H0PESZ1

Dimensions

(Unit: mm)

