



**APC Replacement Battery Cartridge #14**  
Part Number: RBC14



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

### Batteries & Runtime

Battery Type

Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting

Enclosed battery cartridge

Expected Battery Life (years)

3 - 5

RBC™ Quantity

1

Replacement battery cartridge note

RBC 14 is composed of four separate battery cells. The Net dimensions are measured per cell. Due to the weight of this RBC return postage is not included.

### Physical

Net Weight

239.20 lbs. (108.73 kg)

Maximum Height

8.20 inches (208 mm)

Maximum Width

6.50 inches (165 mm)

Maximum Depth

10.20 inches (259 mm)

Shipping Weight

248.00 lbs. (112.73 kg)

Shipping Width

15.50 inches (394 mm)

Shipping Height

20.00 inches (508 mm)

Shipping Depth

27.30 inches (693 mm)

Color

Black

Units per Pallet

4.00

### Environmental

Operating Environment

32 - 104 °F (0 - 40 °C)

Operating Relative Humidity

0 - 95%

Operating Elevation

0-10000 feet (0-3000 meters)
Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
<b>Conformance</b>
Standard Warranty 1 year repair or replace
<b>Sustainable Offer Status</b>
PEP Available in Documentation tab
EOLI Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.