



D


C

B


A



RECOMMENDED PANEL CUTOUT



RECOMMENDED STRIP LENGTH



RECOMMENDED STRIP LENGTH FOR 221221-9 ONLY

1. USE INSTRUCTION SHEET 9089
2. MAXIMUM PANEL THICKNESS: 6.10 [.240]
3. DIELECTRIC MUST WITHSTAND A 6 POUND PUSHOUT FORCE
4. PACKAGED 1 CONNECTOR PER BAG
5. USE CRIMP TOOL: 220190-1

|          |                                         |         |          |          |        |            |            |            |            |          |             |
|----------|-----------------------------------------|---------|----------|----------|--------|------------|------------|------------|------------|----------|-------------|
| OBSOLETE | RG-59/U, 59A/U, 59B/U                   | 58085-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-50428-0  | 221200-3   | 221255-2 | 9-221221-0  |
| OBSOLETE | RG-179/U, 179A/U, 179B/U, 187/U, 187A/U | 58304-1 | 227194-2 | 222001-6 | 329633 | 1-329631-2 | 1-329632-2 | 9-328666-0 | 2-221200-0 | 221255-3 | 1-221221-0  |
| OBSOLETE | AT&T 735A                               | 58174-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-328666-2 | 221200-9   | 221255-3 | 221221-9    |
| OBSOLETE | CUSTOM CABLE: (C&M CABLE 25785)         | 58304-4 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 3-328666-6 | 221200-6   | 221255-4 | 221221-8    |
|          | BELDEN 9240, 9259, 9266                 | 58085-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-50428-0  | 2-221200-5 | 221255-2 | 221221-7    |
| OBSOLETE | RG-59/U, 59A/U, 59B/U                   | 58085-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-50428-0  | 221200-3   | 221255-2 | 221221-6    |
|          | RG-179/U, 179A/U, 179B/U, 187/U, 187A/U | 58304-1 | 227194-2 | 222001-6 | 329633 | 1-329631-2 | 1-329632-2 | 9-328666-0 | 2-221200-0 | 221255-3 | 221221-5    |
| OBSOLETE | BELDEN 8218                             | 58174-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-329461-0 | 221200-9   | 221255-3 | 221221-3    |
|          | RG-59/U, 59A/U, 59B/U                   | 58085-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-50428-0  | 221200-3   | 221255-2 | 221221-2    |
|          | BELDEN 9248 AND MADISON 18AWG           | 58086-1 | -        | -        | 329633 | 1-329631-2 | 1-329632-2 | 9-50427-0  | 3-221200-2 | 221255-1 | 221221-1    |
|          | CABLE                                   | DIE SET | 8        | 7        | 6      | 5          | 4          | 3          | 2          | 1        | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± 0.41 [.016]  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -

MATERIAL  
-

FINISH  
-

DWN  
B. SCOTT  
CHK  
J. LIPPERT  
APVD  
M. PHILLIPS

1-16-91  
1-25-91  
1-25-91

NAME  
JACK.  
BULKHEAD, 75 OHM,  
BNC

SIZE  
A1

CAGE CODE  
00779

DRAWING NO  
221221

RESTRICTED TO  
-

tyco  
Electronics

Tyco Electronics Corporation  
Harriaburg, PA 17105-3608

SCALE  
5:1

SHEET  
1 of 1

REV  
T1