



SECTION 1E

SCREWLESS TERMINAL BLOCKS

WITH EARTH TAB
SCREW TYPE



WITH EARTH CLAW
AND CATCH PINS



Catch pin diameter = 3.5mm

FEATURES

Series 98001 are 3 pole screwless connectors with 2 ports per pole on each side with the option of screw fixing or catch pin fixing (type RZ). There is an additional connection for 1 x 0.5mm² conductor on one side of each pole for internal wiring (eg. interference capacitor).

The range has 4 earthing options:

- without earthing tab (type B)
- earthing tab screw (type SKB)
- earth claw (type SUB)
- earthing bow push in (type STB).

3 pole are marked N, PE, L as standard.

TECHNICAL DATA

Mouldings:	Nylon 6.6, white, UL94 V2
Maximum working temp:	100°C
Current rating:	16 amp to EN60598 24 amp to EN60998
Voltage rating:	450V ~
Tracking distance:	PTI600
External conductor capacity:	2 x 0.5 to 2.5mm ²
Internal conductor capacity:	1 x 0.5 to 2.5mm ² 1 x 0.5 to 1.5mm ² 1 x 0.5mm ²
Recommended conductor stripping lengths:	0.5 to 1.0mm ² 8 + 0.2mm 1.5 to 2.5mm ² 12 + 0.2mm
Interference capacitor:	0.5 mm ² 9 + 0.2mm

OPTIONS

Unmarked: unmarked also available. Details upon request.

Longer lengths: for 4 & 5 pole versions please refer to page 79 & 80.

Strain relief cord grip: for types ZEL980 & ZEL100 please refer to page 81.

APPROVALS

To ENEC10  

CONNECT
metway
NET-WORKS

01273 431600

01273 439288

sales@metway.co.uk

PART NUMBER CODE									
Screw fixing Leave blank Catch pins Enter RZ					No earth tab Enter B Screw earth Enter SKB Push in earth Enter STB Claw Earth Enter SUB				
9	8	0	0	1			0	3	- - -