


4		3	
THIS DRAWING IS UNPUBLISHED		RELEASED FOR PUBLICATION 2017	
© COPYRIGHT 2017 BY - TE CONNECTIVITY ALL RIGHTS RESERVED.			
CONTACT SIZE	MIN. INSUL. OD [mm]	MAX. INSUL OD [mm]	WIRE RANGE [mm ²] REF ONLY
16	.100 [2.54]	.134 [3.40]	14-18 AWG [2.0-.75]

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER PCN E-17-012901	13JUN2017	CM	DM



5. MATERIAL:
PLUG: PPS GF40 (BLACK)
SEAL/GROMMET: VMQ (RED-ORANGE)
CLIP: STEEL, UNPLATED
BOLD: STAINLESS STEEL WITH SILVER PLATING AND MAY TARNISH.


4. MATING TORQUE REQUIREMENT: 25-28 in-lb (2.82-3.16 Nm).

3. THIS PLUG MATES WITH DRC10-40P-XXXX; DRC12-40PXE-XXXX;
DRC13-40PX-XXXX; DRC14-40PXE-XXXX.
CONSULT FACTORY FOR MODIFICATIONS.
X = A, B, C, D KEYS, XXXX = MODIFICATIONS

2. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000.

1. PLUG IS SUPPLIED WITH DUST CAP, 0515-001-4005 (NOT SHOWN)

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 11JUL2000	 TE Connectivity			
DIMENSIONS: INCHES [mm]		CHK B. BYFORD 14FEB2006				
		APVD R. REED 21FEB2006	NAME DRC CONNECTOR PLUG 40 CONTACTS			
		PRODUCT SPEC -	-			
MATERIAL 		APPLICATION SPEC -	SIZE A3			
		WEIGHT -	CAGE CODE 4AFU8			
FINISH -		CUSTOMER DRAWING	DRAWING NO. DRC16-40S			
		SCALE 1.5:1	SHEET 1 OF 1			
			REV J			