



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ KD 10

KD 10

datasheet for KD 10
article number: 930109101



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 109-101
description:	Insulated coupling with a nickel-plated brass tube for two 4 mm diameter plugs.
typ:	KD 10 rot/red
system:	4mm system
order number:	930 109-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	socket (unsprung)
type of termination:	4 mm socket (unsprung)
rated voltage:	30 VAC / 60 VDC
rated current:	10 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PS
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	
	