

3M™ 963 Benchtop Air Ionizer Properties

<u>Typical Properties</u>	
Power Ratings	AC 120V 60 Hz 0.20 A 20 W
Power Inlet	IEC 320 Socket
Power Outlet Cord	6 ft. (1.8 m) cord with IEC 320 and NEMA 5-15 plugs
Dimensions (w/mounting base)	7.0 in. W x 9 in. H x 4 in. D (18 cm W x 23 cm H x 10 cm D)
Weight	2.5 lbs. (1.1 kg)
Air Flow	
<u>Low Speed</u>	
Feet per minute	200 fpm (1.0 m/s)
Standard cubic feet per minute	56.8 scfm
<u>High Speed</u>	
Feet per minute	370 fpm (1.8 m/s)
Standard cubic feet per minute	105 scfm
Operating Temperature	59° F (15° C) to 104° F (40° C)
Static Discharge Time * @ 1 ft. (30 cm)	< 1 second
Certifications and Approvals	UL, C-UL, NOM
Warranty	1 year