



All dimensions are in mm; tolerances according to ISO 2768 c-H

Available variants

Type	"A" (mm)	"C" (mm)	Insertion loss ≤ (dB) at 50 GHz	Marking	Weight (g) / pce
LU8-001-500	500	20±3	2.40	ROSENBERGER WW/YY XXX LU8-001-500	28
LU8-001-750	750	20±3	3.40	ROSENBERGER WW/YY XXX LU8-001-750	35
LU8-001-1000	1000	20±3	4.40	ROSENBERGER WW/YY XXX LU8-001-1000	41
LU8-001-1500	1500	20±3	6.40	ROSENBERGER WW/YY XXX LU8-001-1500	54

WW - week

YY - year

XXX – serial no.

Documents

Technical data sheet connectors

RPC-2.40 plug

09S121-2U1S3

RPC-2.40 jack

09K121-2U1S3

Technical data sheet cable

RTK 125

Assembly parts

Connector left

RPC-2.40 plug

09S121-2U1S3

Connector right

RPC-2.40 jack

09K121-2U1S3

Cable

RTK 125

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/05.10/6.0

Technical Data Sheet				Rosenberger			
Cable assembly - Standardportfolio RPC-2.40 Plug / RPC-2.40 Jack – RTK 125				LU8-001-XXX			
Electrical data							
Impedance		50 Ω					
Frequency		DC to 50 GHz					
Return loss		≥ 16.5 dB, DC to 50 GHz					
Insertion loss		see table available variants					
RF-leakage		≥ 100 dB up to 1 GHz					
Mechanical data							
Minimum bend radius:							
Single		5.10 mm					
Multiple		16 mm					
Environmental data							
Temperature range		-40°C to +85°C					
2002/95/EC (RoHS)		compliant					
Packing							
Standard		1 pce in box					