
[illegible]

| FREQUENCY<br>(MHz) | ATTENUATION<br>dB |
|--------------------|-------------------|
| 5                  | 1dB               |
| 10                 | 3dB               |
| 50                 | 12dB              |
| 100                | 20dB              |
| 500                | 34dB              |
| 1000               | 30dB              |

|             |            |
|-------------|------------|
|             |            |
|             |            |
|             |            |
|             |            |
| 09641247237 | M3         |
| 09641247236 | 4-40UNC-2B |
| Part number | Nut thread |

|       |              |      |                               |              |      |                                                                                                                                  |
|-------|--------------|------|-------------------------------|--------------|------|----------------------------------------------------------------------------------------------------------------------------------|
|       |              |      |                               | Dat.         | Name |  <p>All Dim. in mm<br/>Orig. Size DIN A</p> |
|       |              |      | Detail.                       | 8 - JUL - 02 | CV   |                                                                                                                                  |
|       |              |      | Insp.                         |              |      |                                                                                                                                  |
|       |              |      | Stand.                        |              |      |                                                                                                                                  |
| 31864 | 23/01/04     | AF   | HARTING EURL<br>F-95972 Paris |              |      |                                             |
| 31058 | 8 - JUL - 02 | CV   |                               |              |      |                                                                                                                                  |
| Mod.  | Dat.         | Name |                               |              |      |                                                                                                                                  |



All Dim. in mm  
Orig. Size DIN A 4



D-Sub, male, angled,  
9 Poles, turned solder pin  
tin plated shell and  
metal bracket with nut

TB 0964124723x

Sub.

$$\frac{Mo?Mslob}{Scale}$$

1.5:1

Blatt / Page  
3 / 4