






PANEL THICKNESS	X
0.75–1.25 [0.30–.049]	19.2 [.756]
1.25–2.0 [.049–.079]	19.4 [.764]
2.0–3.0 [.079–.118]	19.8 [.780]



SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
1-1a	OPEN



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY.
 4. RATING: 15A @ 125VAC OR 6A @ 250VAC
 5. MECHANICAL LIFE: 15,000 cycles
 6. ELECTRICAL LIFE: 10,000 cycles
 7. INSULATION RESISTANCE: >1000 Mega Ω
 8. CONTACT RESISTANCE: <20 Mega Ω
 9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles



E-SWITCH®				
TITLE				
R1966A BLK BLK I S				
SCALE	DATE	DR	DWG	REV
1.5:1	12/10/97	MM	M301209	B

B	11664	REVISED PART DESCRIPTION	9/19/01 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			