

You are here: Products » Connectors f.con » PCB connectors » Female headers » BL 15 SMD ... »  

- ▶ Heatsinks f.cool
- ▶ Cases f.case
- ▼ **Connectors f.con**
 - ▶ Sockets
 - ▼ PCB connectors
 - Male headers
 - **Female headers**
 - Direct female connectors
 - Jumpers
 - ▶ IDC-connectors
 - ▶ D-Sub connectors
 - Brackets for PC
 - ▶ Optoelectronics

Female headers


BL 15 SMD ...

BL 15 SMD 089 6

for □ 0.635 mm and up to 0.85 mm Ø

[Data sheet](#)

[add to request](#)



- Features
- Technical Drawing
- Equipping
- Variants
- Service
- Accessories / related products

grid	2.54 mm
no. of contacts	6
contact material	CuZn-alloy
contact sleeve	tin-plated
surface contact / contact sleeve	Ni+4...6µm Sn
contact spring	gold-plated
inner contact spring material	CuBe-alloy
inner contact spring surface	Ni+0,75µm Au
type internal spring	6-fingers
plugability for circuit points	□0,55...0,65mm Ø0,65...0,85mm
insert depth	2.5...6mm
insertion / drawing force	1.3N/0.3N
shock resistance	50 g
volume resistance	≤10 mΩ
vibration resistance max.	15 g
capacity between two adjacent contacts	≤ 0,3 pF
nominal current	3 A
nominal voltage	150 V DC
test voltage	1500 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of inflammability	UL 94 V-0
version	male header
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	SMD
reflow solderable	yes
packing	bar magazine pick and place pad and bar magazine pick and place pad and tape and reel (400pcs/reel)