






ASSEMBLY - VIEW FROM FRONT



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM BOTTOM

ASSEMBLY - VIEW FROM FRONT

### 1583H12C1BKX

Finish - Front - Black Painted Steel

Back - Black Painted Steel

Rated - 125 VAC, 60 Hz, 15 Amps


Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- UL Recognized Standard UL1363

### Cord Length

1583H12C1BKX - 6' Foot Twist Power Cord (NEMA L5-15P)

1583H12D1BKX - 15' Foot Twist Power Cord (NEMA L5-15P)



SECTION A-A

