

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	DWN
						APVD
		D		REVISED PER 0G3B-0008-04	1/12/04	SS
						GS



- 1

BERYLLIUM COPPER.
- 2

PHOSPHOR BRONZE.
- 3

0.76μm [.000030] MIN GOLD OVER 1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN NICKEL.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	2-5-92	tyco Electronics		Tyco Electronics Corporation	
		CHK	2-7-92			Harrisburg, PA 17105	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SOCKET CONTACT ASSEMBLY, #10 AWG, POWER VIII, METRIMATE	
		0 PLC ± -		APVD -		SIZE	
		1 PLC ± -		PRODUCT SPEC		CAGE CODE	
		2 PLC ± -		108-1317		DRAWING NO	
		3 PLC ± .005		APPLICATION SPEC		RESTRICTED TO	
		4 PLC ± -		114-10014		A2 00779 C=213737	
MATERIAL		FINISH		WEIGHT		SCALE	
SOCKET CONTACT: 1		SOCKET CONTACT: 3		-		10:1	
RETAINING RING: 2		RETAINING RING: 4		CUSTOMER DRAWING		SHEET 1 OF 1	
						REV D	