



CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 ~~PA~~ AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:2 Ohm(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V



1PC/PE BAG

⑥	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS"
⑤	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+ "1PC"
④	TIE	1	WHITE L=100mm
③	OUT JACKET	12g	BEIGE (1V-29#) PVC-40P (MOULD NO:WM-40)
②	CABLE	1	BEIGE (1V-29#) USB2.0 UL2725 28#/1P+24#/2C+A/B OD:4.7mm L=3000±10MM
①	CONN	2	USB2.0 A MALE NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE
NO.	NAME	QTY	SPECIFICATION

CNC Tech,LLC			
Industrial Cable and Connector Technology			
DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1020-BE-00300
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	

