



Description

A 6 figure, non-reset counter. Metal/plastic frame assembly assures ruggedness while one piece cover discourages tampering. Precision molded internal gearing requires no lubrication for long, accurate count life. Applications include warranty verification, electronic game counting, coin box tallies, or wherever small size, highly visible numerals, and solid construction are critical.

Features

- Small size
- Highly visible numerals
- Solid construction

Options

- Voltages
- 7 figure
- Lead length
- Special connectors
- Extended temperature range
- Count x 2

Specifications

Figures: 6 figures, white on black, 0.18" [4.6mm] high
Reset: None
Speed: 600 counts/minute
(min. 50ms - on, 50ms - off)
Voltages: 115VAC, 24VDC
(+/- 10%, but not to exceed 10 volts)
Power: 1.5 watts (nominal)

Mounting: Rear, behind the panel, base, or combination
Terminations: (2) #22 AWG 221°F [105°C] wire leads, 10" [254mm] long
Operating Life: Beyond 3 million counts
Temp. Range: +23°F to +104°F [-5°C to +40°C]
Approvals: UL Recognized, CE Compliant
Weight: 2.5 oz. [71g]

Models


Models	Description
2-4416	115VAC, 6 figure, rear mount
8-4416	24VDC, 6 figure, rear mount
R2-4416	115VAC, 6 figure, behind the panel mount
R8-4416	24VDC, 6 figure, behind the panel mount

Models

Models	Description
V2-4416	115VAC, 6 figure, base mount
V8-4416	24VDC, 6 figure, base mount
RV2-4416	115VAC, 6 figure, combination mount
RV8-4416	24VDC, 6 figure, combination mount


Dimensions

Rear Mount




Mounting hole: For M3 screw

Snap-In Panel Mount




Behind the Panel Mount



Mounting holes: For M3 self tapping screw

Base Mount



Mounting holes: 0.14" [3.6mm] Dia.

Applications

Warranty verification



Coin box tallies



Electronic game counting

