

VIDEO LIBRARY

[Video Library](#)

SEARCH

By Type of User:

Select...

By Type of Application:

Select...

By Keyword:

Go

TO PURCHASE

[Request A Quote](#)

[USA Distribution](#)

[International Distributors](#)

[Sales Representatives](#)

[Becoming a Distributor](#)

[Contact Us](#)

DOWNLOADS

[Catalog](#)

Products

[Products](#) > [All Power](#) > [105A12](#)

250 Watt Resistance Soldering Power Unit

Model: 105A12

Used with the following tools:

- [105127 - Standard Tweezer Style Handpiece](#)
- [10541 - Light Tweezer Style Handpiece](#)
- [105133 - Micro Tweezer Style Handpiece](#)
- [105158 - Light Plier Style Handpiece](#)

Included in Systems:

- [10502 - Light Capacity Tweezer-Style Resistance Soldering System](#)
- [10504 - Standard Capacity Tweezer-Style Resistance Soldering System](#)
- [10506 - Light Capacity Plier-Style Resistance Soldering System](#)

Specifications:

- Max Output: 250 Watts
- Power Settings: Infinite
- Connections: Taper pins
- Dim(in): 3¾ x 4½ x 7¼
- Dim(cm): 9.4 x 11.5 x 18.1
- Color: Black

Weight: 7.0 Lbs. (3.18 Kgs)



[+ Add to Quote](#) - [Product Link](#)

American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc.

1177 West Maple Road Clawson, MI 48017-1059 United States -- Phone: 800-550-2510

Copyright © 2000 - 2010 :: American Beauty Tools