

Search within category

GO

BUY NOW

DESIGN / INSTALL

PUR6A04BU-UG



The copper cable is Category 6A (riser CMR) UTP, 4-pair with conductors that are 23 AWG construction with flame-retardant polyethylene insulation. The cable is twisted in pairs, separated by an integrated pair divider, surrounded by a patent-pending MaTriX tape, and protected by a flame-retardant PVC jacket. It is blue and 1000' (305m) long.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
AWG Size	23			
Length (ft.)	1000			
Length (m)	305			
Nominal Diameter (In.)	0.300			
Nominal Diameter (mm)	7.6			
Jacket Material	PE Riser (CMR)			
No. of Pairs	4			
Packaging Type	Reel			
Application	10GBASE-T Ethernet, Data center I/O consolidation, Data center server virtualization, Consolidation of network interconnects, Back-bone aggregation, Parallel processing and high speed computing			
Cable Type	U/UTP			
Flammability Rating	Riser (CMR)			
Nominal Cable O.D. (In.)	0.300			
Nominal Cable O.D. (mm)	7.6			
Part Features	Interoperable, MaTriX technology, Superior headroom warranty, Round cable design, Extended temperature range and Cross-divider			
Performance Level	Category 6A			
Weight (Kg)	16/305m			
Weight (lbs)	35/1000 ft.			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	9,000			