




Panel Mounted Modular Couplers



30 µ Gold
These straight and cross wired modular couplers are useful for connecting modular components. Eight different configurations all fit into the same 0.669" x 0.906" rectangular opening. Wire contacts have 30 microinch gold plating for multiple insertions. Plastic is 94V0 rated. **Color:** Ivory. Flange accepts #4 or #5 mounting screws (recommended 4-40 screws must be purchased separately). Category 3 rated.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0002	ECF504-4C	RJ11, 6 x 4, Crossed	2.72	2.59	2.40
665-0004	ECF504-6C	RJ12, 6 x 6, Crossed	2.62	2.50	2.32
665-0006	ECF504-6CMJ	MMJ, 6 x 6, Crossed	2.81	2.68	2.49
665-0008	ECF504-8C	RJ45, 8 x 8, Crossed	3.51	3.34	3.10
665-0010	ECF504-4S	RJ11, 6 x 4, Straight	2.72	2.59	2.40
665-0012	ECF504-6S	RJ12, 6 x 6, Straight	2.92	2.78	2.58
665-0014	ECF504-6SMJ	MMJ, 6 x 6, Straight	2.81	2.68	2.49
665-0016	ECF504-8SK	RJ45, 8 x 8 K, Straight	3.51	3.34	3.10

30 µ Gold, with 10" Wire Leads
One difficulty in using modular jacks has to do with the mounting problem on a panel. L-com has a solution to the problem, by providing a flange that mounts with two screws in a 0.669" x 0.906" rectangular opening. Choice of RJ11/12 (6 x 6) or RJ45 (8 x 8 K) usable with keyed or non-keyed plugs. Recommended 4-40 mounting screws must be purchased separately.

665-0022	ECJ504-6	RJ11/12, 6 x 6, 10" Leads	2.92	2.78	2.58
665-0024	ECJ504-8	RJ45K, 8 x 8 K, 10" Leads	3.40	3.25	3.02

665-0018. ECF440. Screws PER PK./100 4.29



Panel Mounted USB Type A and B Couplers, 30 µ

This coupler is great for connecting new USB style connectors into panels, etc. One side has type A connector, the other type B conforming to requirements. Recommended 4-40 mounting screws must be purchased separately. **Color:** Black.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0032	ECF504B-UAB	USB A and B Coupler	5.54	5.29	4.91

665-0018. ECF440. Screws PER PK./100 4.29

USB Type A and B Panel Couplers, with 10" Wire Leads


Similar to the coupler above except with wire leads to connect to equipment. Choose from type A or B connectors. Wires are 20 (2 power) and 24 (2 signal) AWG stranded wires with an additional drain to shield. Recommended 4-40 mounting screws must be purchased separately. **Color:** Black.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0042	ECJ504-UA	USB Type A, 10" Leads	5.31	5.07	4.71
665-0044	ECJ504-UB	USB Type B, 10" Leads	5.31	5.07	4.71


665-0018. ECF440. Screws PER PK./100 4.29

Category 5 Keystone Style RJ45 Couplers

Two Category 5 feed-thru modular couplers are available for mating EIA568A or B Category 5 connections. Couplers come in shielded and unshielded version, the unique offset design maintains Category 5 performance and limits depth to only 1.25". Designed to mate with keystone style holes. **Color:** Black.




Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0052	UJ5T568	RJ45, 8 x 8, Unshielded	7.85	7.49	6.95
665-0054	UJ5T568S	RJ45, 8 x 8, Shielded	9.82	9.37	8.70



Category 5 Keystone Style RJ45 16 and 32 Port Panels

These 19" rack panels utilize the UJ5T568 and UJ5T568S couplers listed above. 16 and 32 port versions are available in shielded and unshielded configurations. Category 5 rated. **Color:** Black.



Mini DIN Feed-Thru Adapters

Available in Mini DIN-4, 6, and 8 female/female types. Units are nickel plated brass and utilize a 1/2" "D" hole for mounting. Contacts are gold plated.


Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0072	MD44FF	Mini DIN-4 Adapter, F-F	7.26	6.92	6.43
665-0074	MD66FF	Mini DIN-6 Adapter, F-F	7.55	7.20	6.69
665-0076	MD88FF	Mini DIN-8 Adapter, F-F	7.85	7.49	6.95

Standard IEEE-488 GPIB Cables

The CMB cable series meets all standards of the IEEE-488 interface, conforms with normal mounting procedure and is directly compatible with Hewlett Packard®, AMP® and Amphenol®.



Stock No.	Mfr.'s Type	Length		EACH		
		Meters	Feet	1-9	10-24	25-99
665-0082	CMB24-05M	0.5	1.64	53.27	50.81	47.18
665-0084	CMB24-1M	1.0	3.28	55.85	53.28	49.47
665-0086	CMB24-2M	2.0	6.56	61.04	58.22	54.06
665-0088	CMB24-3M	3.0	9.84	66.22	63.16	58.65
665-0090	CMB24-4M	4.0	13.12	71.40	68.10	63.24
665-0092	CMB24-5M	5.0	16.40	76.58	73.05	67.83
665-0094	CMB24-6M	6.0	19.68	81.76	77.99	72.42
665-0096	CMB24-8M	8.0	26.24	92.13	87.88	81.60




IEEE-488 GPIB Bulkhead Adapters

These bulkhead adapters allow clean feed-thru connections for GPIB systems. Available in either conventional Male-Female or Female-Female configurations.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0102	CIB24BA	GPIB Bulkhead Adapter, M-F	30.52	29.11	27.03
665-0104	CIB24BF	GPIB Bulkhead Adapter, F-F	32.82	31.31	29.07

62.5/125 Micron Multimode Duplex Patch Cords

L-com offers the highest quality 62.5/125 micron fiber optic patch cords. All assemblies use the premium grade connectors with ceramic ferrules and a PC polish. Cable is OFNR riser rated PVC. Custom lengths and types available.



Stock No.	Mfr.'s Type	Description	Length		EACH		
			Meters	Feet	1-9	10-24	25-99
665-0112	FODSTC-01	Dual ST-Dual ST	1	3.28	43.76	41.74	38.76
665-0114	FODSTC-02	Dual ST-Dual ST	2	6.56	45.64	43.53	40.42
665-0116	FODSTC-03	Dual ST-Dual ST	3	9.84	47.51	45.32	42.08
665-0118	FODSTC-04	Dual ST-Dual ST	4	13.12	49.39	47.11	43.74
665-0120	FODSTC-05	Dual ST-Dual ST	5	16.40	52.00	49.60	46.06
665-0122	FODSTC-10	Dual ST-Dual ST	10	32.80	60.64	57.84	53.71
665-0124	FODSTC-15	Dual ST-Dual ST	15	49.20	70.02	66.79	62.02

Stock No.	Mfr.'s Type	Description	Length		EACH		
			Meters	Feet	1-9	10-24	25-99
665-0132	FODSC-01	Dual SC-Dual SC	1	3.28	56.26	53.67	49.83
665-0134	FODSC-02	Dual SC-Dual SC	2	6.56	58.14	55.46	51.50
665-0136	FODSC-03	Dual SC-Dual SC	3	9.84	60.02	57.25	53.16
665-0138	FODSC-04	Dual SC-Dual SC	4	13.12	61.89	59.03	54.82
665-0140	FODSC-05	Dual SC-Dual SC	5	16.40	63.77	60.82	56.48
665-0142	FODSC-10	Dual SC-Dual SC	10	32.80	73.14	69.77	64.78
665-0144	FODSC-15	Dual SC-Dual SC	15	49.20	82.52	78.71	73.09

Stock No.	Mfr.'s Type	Description	Length		EACH		
			Meters	Feet	1-9	10-24	25-99
665-0152	FODST-SC-01	Dual ST-Dual SC	1	3.28	56.26	53.67	49.83
665-0154	FODST-SC-02	Dual ST-Dual SC	2	6.56	45.64	43.53	40.43
665-0156	FODST-SC-03	Dual ST-Dual SC	3	9.84	60.02	57.25	53.16
665-0158	FODST-SC-04	Dual ST-Dual SC	4	13.12	61.89	59.03	54.82
665-0162	FODST-SC-05	Dual ST-Dual SC	5	16.40	63.77	60.82	56.48

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0062	PR175UT568	1.75" 16 Port, Unshielded	172.69	164.72	152.96
665-0064	PR175UT568S	1.75" 16 Port, Shielded	218.76	208.66	193.76
665-0066	PR35UT568	3.5" 32 Port, Unshielded	316.64	302.03	280.46
665-0068	PR35UT568S	3.5" 32 Port, Shielded	403.02	384.41	356.96