


Item no.: 787-722
Product description: 5 A OPEN CIRCUIT AND SHORT CIRCUIT PROTECTED
ADJUSTABLE OUTPUT VOLTAGE LED STATUS INDICATION



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Max. deviation	1 %
Test voltage Pri. - PE	1.5 kV
Test voltage Pri. - Sec.	3 kV
Test voltage Sec. - PE	0.5 kV
Degree of protection	IP 20
Operating temperature	-10 °C ... +70 °C
Storage temperature	-25 °C ... +85 °C
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Weight	900 g
Height	92 mm
Height	3.622 in
Width	75 mm
Width	2.953 in
Depth	136 mm
Depth	5.354 in
Strip length from	8 mm
Strip length to	9 mm

Strip length	0.33 in
Customs Tariff No.	85043180
Country of Origin	China

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected