




Laserliner®

ArcoMaster

Digital electronic angle gauge –
precise, optimal measurements
into the last corner

Rev 0511



1. Precisely measure inside or outside angles from 0-220°: measurements of roof angle, fitting furniture or windows at corners and edges.

2. Additional extensible bevel for measuring angles in difficult to reach locations.

- Robust **aluminium housing**
- **Vertical and horizontal level vials**
- An **illuminated LC display** on each side (front and rear) to permit work at either side.
- Both displays can be flipped at the touch of a button: **FlipDisplay**
- **Auto shut-off function**
- **Auto hold:** for work where the LC display is not visible.
- **Angle bisection** displayed at the touch of a button, even in hold mode; optimal for mitre cuts.

TECHNICAL DATA

VIAL PRECISION	± 0,25 mm/m
ACCURACY	± 0,1°
MEASUREMENT RANGE	0 – 220°
REFERENCE	0°
AUTOSHUT OFF	3 min
LEG LENGTH	40 / 60 cm
POWER SUPPLY	2 x type AA batteries / 8 operating hours
WATER AND DUST PROTECTION	IP 54
WEIGHT	
40:	0.8 / 60: 1.05 kg (incl. batteries)
DIMENSIONS	
40:	420 x 57 x 40 mm (W x H x D)
60:	650 x 57 x 40 mm (W x H x D)



Article no.: 075.130A

EAN-Code: 4 021563 664016

ArcoMaster 40
inclusive soft bag
+ batteries

Packing dimension (W x H x D)
460 x 310 x 130 mm

PU 5

Article no.: 075.131A

EAN-Code: 4 021563 666683

ArcoMaster 60
inclusive soft bag
+ batteries

Packing dimension (W x H x D)
650 x 310 x 130 mm

PU 5



Bevel extended down-
ward



.... or upward,
as needed.



LC display on the front
and rear side



Display flips 180° at
the touch of a button