




~DIN 84 A

~ISO 1207

Standard withdrawn

**BN 532****Slotted cheese head machine screws**

Brass

plain

- ~UNI 6107
- ~ČSN 021131



All lengths fully threaded

Article#	d ₁	d ₂	k	n	t min.	L
1159690	M1	2	0,7	0,25	0,25	2
1159704						3
1159712						4
1159720						5
1159739						6
1159747						8
1159755	M1,2	2,3	0,8	0,3	0,3	2
1159763						3
1159771						4
1159798						5
1159801						6
1159828						8
1159836	M1,4	2,6	0,9	0,3	0,4	2
1159844						3
1159852						4
1159860						5
1159879						6
1159887						8
1159895						10
1159909						12
1159917	M1,6	3	1	0,4	0,45	2
1159925						3
1159933						4
1159941						5
1159968						6
1159976						8

Article#	d ₁	d ₂	k	n	t min.	L
1159984	M1,6	3	1	0,4	0,45	10
1159992						12
1160001						(14)
1160028	M2	3,8	1,3	0,5	0,6	2
1198505						3
1198513						4
1198521						5
1198548						6
1198556						8
1198564						10
1160036						12
1160044						(14)
1160052						16
1160060						(18)
1160079						20
1160095						25
1160109						30
1198955	M2,5	4,5	1,6	0,6	0,7	4
1198963						5
1198971						6
1198998						8
1199005						10
1199013						12
1160117						(14)
1160125						16
1160141						20
1160176						25
1160184						30
1199242	M3	5,5	2	0,8	0,85	3
1199250						4
1199269						5
1199277						6
1199285						8
1199293						10
1199307						12
1160192						(14)
1199323						16
1199358						20
1199374						25
1199382						30
1160222						35

Article#	d ₁	d ₂	k	n	t min.	L
1160230	M3	5,5	2	0,8	0,85	40
1160249						45
1160257						50
1160265						60
1199633	M4	7	2,6	1,2	1,1	5
1199641						6
1199668						8
1199676						10
1199684						12
1160281						(14)
1199706						16
1199722						20
1199730						25
1160311						30
1160338						35
1168827						40
1160346						45
1160354						50
1160362						60
1160389	M5	8,5	3,3	1,2	1,3	6
1199935						8
1199943						10
1199951						12
1160397						(14)
1199986						16
1200003						20
1200038						25
1200046						30
1160419						35
1160427						40
1160435						45
1160443						50
1160478	M6	10	3,9	1,6	1,6	8
1200135						10
1200143						12
1200178						16
1200194						20
1200216						25
1200224						30
1200240						40
1160486						50

Article#	d ₁	d ₂	k	n	t min.	L
1160494	M6	10	3,9	1,6	1,6	60