




LOC	DIST	REVISIONS				
CM	52	P	LTR	DESCRIPTION	DATE	APVD
		V		REV & REDWN PER EC 0L30-0146-97	5-15-97	TB RS

- 1 0.00076 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE OVER NICKEL OVER ALL UNDERPLATE.
2. WIRE RANGE: 0.12 - 0.4 MM² (26 - 22 AWG)
3. INSULATION RANGE: 0.89 - 1.65


POINT OF MEASUREMENT
1 90° FROM SEAM



SECTION A-A



SECTION B-B




SECTION C-C

1	0.25 BE COPPER	60888-4
MATTE TIN	0.25 BE COPPER	60888-3
2	0.25 PH BRZ	60888-2
PRE-TIN	0.25 PH BRZ	60888-1
FINISH	MATERIAL	PART NUMBER

1.359	.0535	1.91	.075	2.79	.110	-	-
1.02	.040	1.65	.065	2.67	.105	-	-
0.89	.035	1.63	.064	2.41	.095	9.65	.380
0.25	.010	1.486	.0585	2.29	.090	6.55	.258
0.13	.005	1.47	.058	2.06	.081	6.40	.252
0.00076	.000030	1.40	.055	1.96	.077	3.94	.155
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

SEE TABLE

FINISH

SEE TABLE

DWN
T. BECK
5-15-97

CHK
R. SWING
5-15-97

APVD
A. BEDDICK
8-08-97

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
RECEPTACLE, .058 DIAMETER,
26-22 AWG, .035-.065
INSULATION, P.C. CONTACT

SIZE
A2

CAGE CODE
00779

DRAWING NO
60888

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
V