


Interface Module

1/1

Interface module for ribbon cable acc. to IEC 603-1 / DIN 41651

Preliminary data sheet


Description	Item-No.	Pack.-unit pcs
For mating connectors with IDC	289-615	1
Interface module with male connector for femal connector acc. to DIN 41651 part 1 and 2. Short and long latches for the female connector with and witout strain relief, are shipped lose. • Mounting carrier for DIN 35 rail with lateral marking system. • Marking with the WMB multi marking system or with marking strips with cover.	Technical Data	
	Operating voltage	AC/DC 125 V
	Nominal current	1 A
	Connector contact	Phosphor-bronze
		0.38 µm Au selektivly over 1.3 µm Ni
	Performance level	3
	Nominal voltage	
	acc. to VDE 0110/1.89	125 V / 1.5 kV / 2
	Dimensions incl.	
	mounting carrier (LxWxH)	(55x85x34*) mm (1.57x3.35x1.34*) in
		* from upper edge of DIN 35 rail
	Wire connection	CAGE CLAMP® terminal strips
		(WAGO series 737)
		0.08-2.5 mm² / AWG 28-12 **
		** AWG12: THHN, THWN
	Stripped length	5-6 mm / 0.22 in
	Mating direction	vertical
	Ambient operating temperature	-20 °C...+55 °C
	Storage temperature	-40 °C...+70 °C