

XS Trackball Keyboard

G84-5400



Slim, compact keyboard with integrated optical Trackball. Cherry Gold Crosspoint individual keys ensure operational reliability and durability. For industrial applications, in IT, Point of Sale and medical facilities. Easy installation and fixation e.g. in kiosks and keyboard drawers.



Facts & Features

- Single keys with Gold Crosspoint contacts (Cherry ML Technology)
- Designed for continuous use – more than 20 Mio. key operations
- High reliability and uniquely precise tactile keying
- Integrated optical Trackball plus 2 mouse buttons
- Ultra slim - overall height only 20 mm
- 88/89 keys with full functionality of a standard keyboard
- Usable with standard drivers of the operating system
- Supports Code Set 3 and UnifiedPOS
- Installation and fixation options, dimension identical to G84-5200, G84-5500
- Pluggable feet
- Fast switch-over to numeric block via Fn key
- Programmable keys
- Ideal for use with space limitations and for 19" applications
- WetEx™ flexible protective skin available
- Available in various country versions and also without housing for OEM

Agency Approvals / Instructions

- CE, VDE, cURus, FCC, VCCI, C-Tick, BSMI, WHQL, WEEE, RoHS

Technical Data

- Interface
USB plug or 2x PS/2
- Cable Length
approx. 2.50 m
- ML Gold Crosspoint Keys
Key life: > 20 Mio. operations
Key travel: 3 mm
- Layout
Interkey Spacing: approx. 18 mm
88 / 89 keys for internat. / europ. layout
- Trackball
Ball size: 14 mm (5.5") Ø, black
Sensing: optical sensor
Resolution: 400 dpi
Lifetime: Ball > 80 km
Button > 3 Million operations
- Weight
Net: 540 g
Gross: 670 g
- Dimensions
Keyboard: 374 x 139 x 20 mm
Packaging: 393 x 196 x 33 mm
- Current Input
typ. 35 mA
- Reliability
MTBF > 8.6 Million hours
- Operating Temperature
0°C to +40°C
- Storage / Transport Temperature
-40°C to +65°C
- Packaging Unit
21 keyboards per master carton
12 master cartons per pallet (252 pcs.)
- Warranty
2 years



Environmental Conditions / EMC

- IEC 60068-2-6 (vibration)
- IEC 60068-2-27 (shock)
- IEC 60068-2-3, -30 (constant atmosphere)
- IEC 60068-2-14, -33 (alternating atmosphere)
- EN 55022 class B (RF emissions)
- EN 55024 / EN 61000-4-2, -3, -4, -6 (RF immunity)

System Requirements

- PS/2: Plugs for Keyboard & Mouse
- USB: USB plug & supporting operating system

Delivery Volume

- Keyboard, pluggable feet, manual

Order Description

<i>Order Number</i>	<i>Interface</i>	<i>Colour</i>
G84-5400LPMxx-0	2x PS/2	light grey
G84-5400LPMxx-2	2x PS/2	black
G84-5400LUMxx-0	USB	light grey
G84-5400LUMxx-2	USB	black

The xx in the order number defines the country version as follows:

Possible European layouts:

BE	Belgium
CH	Switzerland
DE	Germany
DK	Denmark
ES	Spain
FR	France
GB	UK-English
HU	Hungary
IT	Italy
NO	Norway
PL	Poland
PO	Portugal
SF	Sweden / Finland
SK	Slovakia
TS	Czech Republic
TQ	Turkey

Possible international layouts:

EU	US English with €
----	-------------------

Other country versions upon request.

ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA
Phone: 262.942.6500
Internet: www.cherrycorp.com

Sales: 262.942.6562
E-Mail: CEP_sales@ZF.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2013 ZF Electronic Systems Pleasant Prairie, LLC
Last update: February 14, 2013