


1.00
[25.4]


0.42
[10.7]

SEE NOTE 5

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY
PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE.
AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH
THESE MOUNTS MAY BE APPLIED AND / OR THE SURFACE
TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS
ABM100-AT	0.26 (119)	M, I, S



-ADHESIVE BACKING: ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2. THE '-AT' SUFFIX REPRESENTS ACRYLIC ADHESIVE.
3. MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).
4. SUPPLIED IN STRIPS OF TWO.
5. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

CAD FILENAME/LAYERS

G00033BB_DC_ABM100AT_06

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

ABM100-AT
FOUR-WAY MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MJK

MAT'L:

SCALE	NONE
-------	------

DATE	12/09/92
------	----------

NYLON 6/6

DRAWING NO.

GB0033BB

DWG
A
SIZE

6	8-24-05	TMSA		REMOVED PART NUMBER ABM25B REVISED WINDOW DIMENSIONS	6B0033BB	6				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			